

Spectral Glaze Finishing putty

Two component multifunctional putty

RELATED PRODUCTS

Betox 50E Hardener

PROPERTIES

- Putty contains modern light nanofillers
- Product has smooth and self-levelling surface
 - Pinnholes free
- The colour changes as polymerisation proceeds
- Sanding without edge between putty and sheet metal
 - Superb sanding



Spectral Glaze Technical data sheet 2023-11-07

SUBSTRATES				
Old paint coatings	Degrease, dry sand P220 ÷ P280, degrease again.			
Polyester laminates	Degrease, dry sand P80 ÷ P120, degrease again.			
Steel	Degrease, dry sand P80 ÷ P120, degrease again.			
Galvanised steel	Degrease, matt with an abrasive needled cloth, degrease again.			
Aluminium	Degrease, matt with an abrasive needled cloth, degrease again.			
Two-component acrylic primers	Degrease, dry sand P220 ÷ P280, degrease again.			
UNDER 305-00	Degrease, dry sand P220 ÷ P280, degrease again.			
UNDER 385	From 90 minutes to 12 h at 20°C: without sanding Over 12 h: degrease, dry sand P220 ÷ P280, and degrease.			
UNDER 385-00	From 30 minutes to 12 h at 20°C: without sanding Over 12 h: degrease, dry sand P220 ÷ P280, and degrease.			
Caution: Do not apply the putty directly on wash primers or one-component acrylic and nitrocellulose products.				
MIXING RATIO				
		Volume ratio	Weight ratio	
	Spectral Glaze	100 ml	100 g	
	HARDENER	2 ml	2 g	
CONTENT OF VOLATILE ORGANIC COMPOUNDS				
VOC II/B/b limit *	250 g/l			
Actual VOC content	90 g/l			
* For ready to apply mixture compliant with Directive UE 2004/42/CE				
APPLICATION CONDITIONS				
The putty should be applied at a temperature above +10 °C.				
APPLICATION				
	Clean and sand the surface.			
	Degrease with Spectral EXTRA 785.			
	Mix the components thoroughly until obtaining a uniform colour. Observe the required amount of hardener. The putty colour changes gradually from blue through "grey" to white.			
	It is advisable to use a putty dispenser in order to obtain the appropriate component ratio.			
	Apply the putty. Maximum layer thickness: 3mm.			



Spectral Glaze Technical data sheet

		2023-11-07	
	3 ÷ 6 minutes/20°C		
	3-6 minute after mixing components patchy colour of putty means inaccurate mixing components		
DRYING TIMES			
	20°C	60°C	
	20 ÷ 30 minutes	10 minutes	
CAUTION: Drying times apply to the tem	peratures of the individual elements.		
DRYING WITH AN INFRARED RADIAT	OR		
	Distance	Follow the recommendations of the equipment manufacturer.	
	Time depending on the type and power of the lamp	Approximately 5 min.	
SANDING			
0	Rough	P120 ÷ P150	
	Finish	P180 ÷ P240	
COLOUR			
Blue in can. White after hardening			
EQUIPMENT CLEANING			
NC solvent, Thin 880, acetone			
STORAGE CONDITIONS			
Store in a dry and cool room, away from Avoid direct exposure to sunlight.	sources of fire and heat.		
SHELF LIFE			
Spectral Glaze	12 months/20 °C		
HARDENER	18 months/20 °C		
SAFETY			
See Safety Data Sheet.			
OTHER INFORMATION			

OTHER INFORMATION

Registration number: 000024104

The effectiveness of our systems results from laboratory research and many years of experience. The data contained herein meets the current knowledge about our products and their application potential. We ensure high quality, provided the user follows the instructions and the work is performed in accordance with good workmanship. It is necessary to do a test application of the product due to its potentially different reaction with different materials. We may not be held liable for defects if the final result was affected by factors beyond our control.